




Meiko Topline 30

Wall mounted bedpan washer-disinfector ideal for residents and patient's bedrooms



Features

- Work safely in a hygienic environment with no risk of germ discharge with TopLine 30s patented complete steam impermeability system
- Controllable main telescopic rotary nozzle to optimise internal cleaning of the care utensils
- Power nozzle system provides thorough cleaning performance
- Air drying and cooling with HEPA filter (which is easy to access and replace) ensures hygienically clean results
- TopLine 30 protects the system from recontamination through disinfection of all water carrying channels
- Guarantee disinfection safety through patented control of the freely selectable A0 value (60 to 3000) and monitoring of temperature sensors which cross check their readings
- TopLine 30 ensures hygienic safety due to the A0 value control system to DIN EN ISO 15883
- System display on the unit achieves visibility of actual and target A0 value
- Supply disconnection to EN 1717 type AA
- TopLine 30 achieves short programme cycles with an integrated steam generator/water tank
- Advanced control system to monitor and assess the disinfection process through temperature sensors
- Universal basket & trays provide optimum use of washing chamber and versatility
- TopLine 30 WC with integrated WC connection (WC not included)

Product Code	Product Description	Pack Size	Quote
MWC-10-0000006 16	TopLine 30 Wall Mountable Bedpan Washer-Disinfector	ea	
MWC-10-0000006 16-WC	TopLine 30 Flush Wall Mountable Bedpan Washer with integrated WC connection	ea	

Relevant Product

- [Asepti Synergy WD, 5 L](#)
- [Asepti Autozyme Pr, 5 L](#)
- [Asepti Synergy 5, 5L](#)
- [Asepti Wash, 5L](#)

- [Asepti Sonic, 5L](#)
- [Asepti RHW, 5L](#)
- [Asepti Rinse Clean, 5L](#)

Applications

- Infection Control
- Healthcare Facilities
- Residential Aged Care

Resources

- Video
- Video
- Brochure